

Thermo Scientific Masterflex B/T

Analog or Digital Variable-Speed Systems



B/T Analog Pump System

- Simple one-hand opening/closing.
- Reinforced base and motor mount with return bend for easy installation.
- Achieve the highest flow rates of any Masterflex pump — up to 37 LPM (9.8 GPM).
- Simple controls make this easy-to-operate.
- Washdown pumps handle the toughest process and production applications, then clean up with ease.
- Detachable controller with 3 m (10 ft) cord mounts on pump or wall.
- IP56-rated motor protects against dust and strong jets of water.
- Reversible motor: purge before or after pumping, pump fluid in either direction.
- Includes 6 ft line cord – 115 V AC: US Standard plug; 230 V AC European plug.

B/T Digital Modular Pump System

- Simple one-hand opening/closing.
- Reinforced base and motor mount with return bend for easy installation.
- High-volume, high-accuracy dispensing.
- Dispense by volume or time, or pump continuously.
- Separate motor and controller by up to 25 feet for convenient operation.
- IP56-rated controller and motor protect against dust and water.
- Keypad lock/unlock feature helps lock in your settings and prevents accidental or unauthorized changes.
- Simple intuitive controls. Start, stop, prime, reverse, calibrate, and dispense using the sealed keypad.
- Display shows flow rate in metric or units (LPM).
- Calibrate pump for optimal accuracy.



2 year
warranty

